

Immersion Assembly for pH and Redox Sensors *DipFit P CPA 140*

**Immersion assembly with flange connection for
demanding processes.**

Sensor holder with bayonet lock



Areas of application

- pH/Redox measurements in the chemical industry, for example for
 - production of synthetic materials and dyes,
 - production of pesticides and fertilisers;
- pH/Redox measurements in the petrochemical industry, for example for
 - separation of oil and waste water,
 - treatment of condensates;
- pH measurements in the pharmaceutical and cosmetic industries, for example for
 - production of soap,
 - production of proteins,
 - lipolysis;
- pH/Redox measurements in power plants and waste incinerating plants, for example for
 - monitoring of cooling water,
 - scrubbing of exhaust gases;
- pH/Redox measurements in extractive metallurgy and metal processing

Benefits at a glance

- Simple installation and removal of the electrode holder due to the bayonet mounting method
- Good sealing, even in media containing solid particles, due to the bayonet mounting method
- Suitable for use at high pressures and temperatures (up to 10 bar and max. 150 °C)
- Immersion length from 500 to 2500 mm
- Integrated potential matching pin made of Hastelloy C4 or tantalum
- Reduced condensation due to an active-breathing Goretex® filter
- Three mounting positions for pH, Redox and temperature sensors plus a cleaning head
- Spray and ultrasonic cleaning can be retrofitted easily
- Flexible connection to the process by means of various flanges (DIN, ANSI, JIS)

Quality made by
Endress+Hauser




ISO 9001

Endress + Hauser

Nothing beats know-how




Stainless steel version




Stainless steel version

Dimensions of fixed flange




	Flange		
	DN 80 PN 16	ANSI 3" 150 lbs	JIS 10K 80A
D	200	190,5	185
Ø k	160	152,4	150
d ₂	18	19	19
b	20	23,8	18
a	63,5	63,5	63,5
Screws	M 16	M 16	M 16

Section A-A




Bayonet mounting



Dimensions of the stainless steel assembly
DipFit P CPA 140

- 1 Assembly head
- 2 Cable gland Pg 13.5
- 3 Screw-in lifting eyes
- 4 Fixed flange
- 5 Electrode holder
- 6 Shock-protection studs (stainless steel 1.4401)
- 7 Goretex® filter

PVDF version




Bottom view of electrode holder with one electrode installed and potential matching pin



Top view of the electrode holder with one electrode installed

PVDF version


Dimensions of loose flange



	Flange		
	DN 80 PN 16	ANSI 3" 150 lbs	JIS 10K 80A
D	200	200	185
Ø k	160	152	150
d ₂	18	19	19
b	22	22	18
a	110	110	110
Screws	M 16	M 16	M 16

Dimensions of the PVDF assembly DipFit P CPA 140


- 1 Assembly head
- 2 Cable gland Pg 13.5
- 3 Loose flange
- 4 Electrode holder
- 6 Shock-protection studs
- 7 Goretex® filter



Accessories

KCl reservoir CPY 7:

- 1 Valve
- 2 Dummy plug; reference electrode position
- 3 Dummy plug; manometer position
- 4 Filling mark
- 5 Securing nut for electrolyte vessel
- 6 Hose coupling



KCl reservoir mounted on top of the assembly CPA 140

KCl reservoir

- for supplying liquid filled pH electrodes with KCl electrolyte
- maximum effective volume 200 ml
- available with wall-mounting bracket or
- direct mounting on assembly without further securement

Technical data

General data

Manufacturer	Endress+Hauser
Designation	DipFit P CPA 140

Installation

Immersion length	500 ... 2500 mm
Electrode length	120 mm
Number of mounting positions in sensor holder	3 cable glands Pg 13.5
Required installation cross-section	DN 80
Cable gland	2 cable gland Pg 16; 1 cable glands Pg 13.5

Mounting

A	Without flange
B	Flange DN 80 PN 16
D	Flange ANSI 3", 150 lbs
E	Flange JIS 10K 80A

Weight

PVDF (500 mm / 2500 mm)	Approx. 2.5 kg / approx. 3.0 kg
Stainless steel 1.4404 (500 mm / 2500 mm)	Approx. 8.0 kg / approx. 12.0 kg

Materials in contact with medium

Immersion tube	PVDF / stainless steel 1.4404
O rings	EPDM / Viton / Chemraz / Fluoraz

Sensor holder

Sensor holder	PVDF / stainless steel 1.4404
Potential matching pin	Hastelloy C4 / tantalum
Shock-protection studs	PVDF / 1.4401
Dummy plugs	PEEK

Materials not in contact with medium

Protective cap	PP-GF 20
Protective cover for KCl reservoir	Stainless steel 1.4571
Screw-in lifting eyes	Stainless steel 1.4301

Operating data


Operating pressure

PVDF version	Max. 6 bar (at 20 °C)
Stainless steel 1.4404 version	Max. 10 bar

Operating temperature

PVDF version	0 ... +120 °C
Stainless steel 1.4404 version	-15 ... +150 °C (EPDM 140 °C)

Pressure / temperature diagram



Note

The operating limits of the entire system are determined by the operating limits of the individual components

used (assembly, sensors, cables, accessories, etc.)!

Subject to modifications.

How to order

Immersion assembly DipFit P CPA 140

Assembly/PAL material

21 PVDF / PAL: Hastelloy C4
22 PVDF / PAL: tantalum
30 Stainless steel 1.4404

Immersion length

1 500 mm
2 1000 mm
3 1500 mm
4 2000 mm
5 2500 mm

Process connection

A Without flange
B Flange DN 80 PN 16
D Flange ANSI 3"
E Flange JIS 10K 80A

Gasket material

1 EPDM
2 Viton
3 Chemraz
4 Fluoraz

Features

10 Basic version
30 Test certificate to EN 10204-3.1B

CPA 140-

complete order code

Accessories

O-ring sets	
– EPDM	Order No. 50089296
– Viton	Order No. 50089297
– Chemraz	Order No. 50089298
– Fluoraz	Order No. 50089299

For more Endress+Hauser product please visit: www.ainstru.com
Mail: Sales@ainstru.com

Endress+Hauser GmbH+Co.
- Instruments International -
P.O. Box 2222
D-79574 Weil am Rhein
Tel. (07621) 975 - 02
Fax (07621) 975345